








RoHS



PCB Layout (Pattern Side)



Circuit Diagram



Product No. : TS-064SA-□□-□□

型号:

产品高度(H):—
015=1.5mm
017=1.7mm

└: 包装方式
-P=编带(非编带, 不启用)

└: 弹片
D2=SUS/1PCS
D4=SUS/2PCS

操作力度：
180=180gf±50gf
250=250gf±50gf

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		2	Phosphor bronze	Silvering
Ⓓ	Reed		2	SUS	Silvering covered
Ⓒ	Base		1	LCP	White
Ⓑ	Cover		1	SUS	
Ⓐ	Button		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
— 众迪 —

Zhongdi Electronic Technology Co., Ltd

design

	date
--	------

TACT SWITCHS

Review

	date
--	------

name

TACT SWITCHES

Appro

	date
--	------

model

TS-064SA-□□-D□

modify

Review

Approved

angle	$\pm 2^\circ$
10~30	± 0.30
5~10	± 0.20
~ 5	± 0.10

	Appr
Drawing number:	

Proportion

1:1

	u
--	---

nit	
-----	--

mm

	gape
--	------

the number

ber	
-----	--

--	--

--	--

A4	+
----	---



项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	100,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.15±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® Zhongdi Electronic Technology Co., Ltd											
design		date		name		TACT SWITCHS					
Review		date									
Approved		date		name		TS-064SA-□□-D□					
number:											
1:1		unit	mm	gape number						A4	