







RoHS



PCB Layout (Pattern Side)



TOTAL HEIGHT	
Code	H
015	1.5
017	1.7

Product No. : TS-064SA-□□-□□

型号: ————

产品高度 (H) : ————
015=1.5mm
017=1.7mm

操作力度: ————
180=180gf±50gf
250=250gf±50gf

—: 包装方式
—P=编带 (非编带, 不启用)


—: 弹片
D2=SUS/1PCS
D4=SUS/2PCS

Ⓕ	Dust film	1	Polyimide tape	
Ⓔ	Terminal	2	Phosphor bronze	Silvering
Ⓓ	Reed	2	SUS	Silvering covered
Ⓒ	Base	1	LCP	White
Ⓑ	Cover	1	SUS	
Ⓐ	Button	1	LCP	Black

<					
--	--	--	--	--	--

Drawing number: ————

Proportion 1:1 unit mm gage number ————



modify Review Approved Tolerance not specified

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	100,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.15±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd									
design				date				name		TACT SWITCHS									
Review				date															
Approved				date				name		TS-064SA-□□-D□									
number:																			
1:1		unit		mm		gape		number											
										A4									