









PART NO	PIN	A	B
GH1.5-2PLT	2	1.5	7.5
GH1.5-3PLT	3	3.0	9.0
GH1.5-4PLT	4	4.5	10.5
GH1.5-5PLT	5	6.0	12.0
GH1.5-6PLT	6	7.5	13.5
GH1.5-7PLT	7	9.0	15.0
GH1.5-8PLT	8	10.5	16.5
GH1.5-9PLT	9	12.0	18.0
GH1.5-10PLT	10	13.5	19.5
GH1.5-11PLT	11	15.0	21.0
GH1.5-12PLT	12	16.5	22.5
GH1.5-13PLT	13	18.0	24.0
GH1.5-14PLT	14	19.5	25.5
GH1.5-15PLT	15	21.0	27.0

SPECIFICATIONS

Applicable Wire: AWG.#30~#24

Voltage rating : 100V DC/AC

Current rating: 2A (AWG.#24)

Withstand voltage: 500V AC/min.

Working Temp : -40°C ~ +85°C

Insulation resistance: ≥500 MΩ

Contact resistance: ≤20 mΩ

MATERIAL

Insulator: Glass-Filled Polyamide,UL94-V0

Contact PIN: Phosphor Bronze

Solder tab: Phosphor Bronze

备注:所有原料,零部件均符合最新ROHS2.0及REACH

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 压接式连接器	
			PAR	GH1.5-NPLT
			DWN	Lucas
			CHKD	Ethan
			APVD	Jacob
DECIMALS:	ANGLES:		SCALE:1:1	UNIT:MM
X.:±0.20	X.':±5°		CUSTOMER COPY	SIZE:A4
X.X:±0.10	X.X':±3°			
X.XX:±0.05	X.XX':±1°		SHEET:1F1	REV:A