

为 您 的 产 品 保 驾 护 航

PRODUCT DATASHEET

Blade Fuses


0287 Blade Fuse Devices



Description

The 0287 Blade Fuses are the standard for vehicle circuit protection. Its miniature design meets the need for more circuits to be protected while utilizing less space, and its ability to cope with high temperatures in adverse environments makes the 0287 blade fuse of recommended choice for protection.

Dimensions (mm)



Electrical Characteristics


% of Rating	Opening Time
110	4h min
135	0.75s~1800s
200	0.15s~5s
350	0.04s~0.5s
600	0.02~0.1s

Performance Specification


Model	Current Rating (A)	Interrupting Rating	Voltage Rating	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	Housing Material Color
0287001.J	1.0	1000A @32VDC	32V DC	225	59.4	灰绿色
0287002.J	2.0			200	43.9	灰色
0287003.J	3.0			175	30.7	玫红色
0287004.J	4.0			175	21.4	玫瑰色
0287005.J	5.0			175	16.1	橙色
028707.5J	7.5			150	11.0	褐色
0287010.J	10.0			125	8.4	红色
0287015.J	15.0			125	5.7	浅蓝色
0287020.J	20.0			125	4.5	黄色
0287025.J	25.0			110	3.5	透明色
0287030.J	30.0			100	2.9	浅绿色
0287035.J	35.0			90	2.6	深紫色
0287040.J	40.0			85	2.3	粉红色
0287045.J	45.0			80	2.0	浅紫色
0287050.J	50.0			75	1.8	浅玫红色

Environmental Characteristic

Temperature Rerating Curve



Average Time-Current Curve



Specification

Operating Temperature	Terminals	Housing Material
-40°C~+125°C	zinc alloy	PA66

Packaging Quantity

Model	QTY
0287 Series	1000 pcs/bag