

为 您 的 产 品 保 驾 护 航

PRODUCT DATASHEET

Blade Fuses

0299 Maxi Blade Fuse Devices



Description

The 0299 Maxi Blade Fuses standard applies to vehicle series fuses below 32V.


Performance Specification

Model	Current Rating (A)	Interrupting Rating	Voltage Rating	Max.Voltage Drop(mV)	Cold Resistance (mΩ)	Housing Material Color
0299020.J	20	1000A @32VDC	32V DC	125	16	黄色
0299030.J	30			100	10	浅绿色
0299040.J	40			100	8.0	桔黄色
0299050.J	50			100	5.0	红色
0299060.J	60			100	4.8	浅蓝色
0299070.J	70			100	4.5	棕色
0299080.J	80			100	4.3	无色
0299100.J	100			100	4.2	紫色

Time-Current Characteristics



% of Rating	Opening Time
100%	100h min
135%	60s~1800s
200%	2s~60s
350%	0.2s~7s
600%	0.04s~1s

Temperature Rerating Curve



Time-Current Characteristic Curves

Dimensions (mm)



Specification

Operating Temperature	Terminals	Housing Material
-40°C~+105°C	zinc alloy	PC

Packaging Quantity

Model	QTY
0299 Series	100 pcs/bag