









RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05

pin number	pin name
G1	switth
pin 8	RSV
pin 7	DD
pin 6	VSS
pin 5	SCLK
pin 4	VDD
pin 3	DI
pin 2	CS
pin 1	RSV

注解:

1. 素材要求:

- 1.1 胶芯: LCP 30%GF, 防火等级: UL94V-0. 颜色: 黑色;
- 1.2 端子: C5191-H, T=0.15MM
- 1.3 外壳: SUS201 1/2H, T=0.20MM

2. 电镀要求:

- 2.1 端子: 接触区镀金1U", 焊脚区域镀锡100~120U", 全部区域电镀镍底50U".

3. 电气性能要求:

- 3.1 额定电流 1.0A. 额定电压 30V
- 3.2 耐压交流电压最小100VAC.
- 3.3 绝缘电阻最小100M 欧姆.
- 3.4 接触电阻最大50 毫欧.

4. 环境性能要求:

- 4.1 使用环境-30摄氏度~80摄氏度
- 4.2 部件耐热焊接温度符合230摄氏度30~60秒, 260摄氏度10秒要求.

5. "△" 为QC重点量测尺寸

6. "⊗" 为FAI量测尺寸

7. 部件符合RHOS 2005/95/EC.




深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30
X.XX ±0.25
X.XXX ±0.15

X' ±2" X.X' ±0.5"



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

悬空式T卡座带检测P 2.3H

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW144-TF09-230B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2207051620

SHEET NO.

1 OF 1