







Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	3.80	2.50	6.50	6.30
Alternate				



PZ 200 - * - N - S - * - ** - * - P

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type S=直插 D=贴片 S-D=贴片	Length (Plastic) (塑包)	Contact G0:Gold G1:1u Gold G2:3u Gold G3:5u Gold G4:10u Gold G5:15u Gold G6:30u Gold G7:Gold Flash/Tin	Plating Flash Gold Gold Gold Gold Gold Gold Flash/Tin	R=Reel +Cap (编带+包胶)	Post (带柱)
---	------------------------	--------------------------------	-----------------------------	--	--	---------------------------	--------------

电子城

			GENERAL TOLERANCE	审图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM TOL	审核 CHECK	工程专用章				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.00双排 排针 贴片 编带+盖 (塑高2.0)	版本 REV.	A	
1	初版发行		X.XX ±0.20		产品料号 PART NO.	PZ200-2-N-S-2.0-XX-R	单位 UNITS	mm	
			X.XXX ±0.10	比例 SCALE					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection		材料 MATERIAL	页次 SHEET	1/1	