





序号	品名	材质
①	0.8—C型WTB 刺破型公头脱芯	LCP UL94 V-0 米黄色
②	0.8—C型WTB 刺破型公头端子	铜合金/镀金



1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$ (含通电时的温度上升值)。
3. 额定电压：30V, AC/DC。
4. 接触电阻：初期 $\leq 0.02\Omega$ ，环境试验后 $\leq 0.04\Omega$ 。
5. 绝缘电阻： $\geq 100\text{M}\Omega$ min。
6. 额定电流：0.5A, AC/DC
(使用AWG#32, O.D. $0.38 \pm 0.02\text{mm}$)。
7. 耐电压：AC 200V/1分钟。

Part No	CKT	A	B	C	D
WF-1D008B2P	2	0.80	1.78	2.18	2.40
WF-1D008B3P	3	1.60	2.58	2.98	3.20
WF-1D008B4P	4	2.40	3.38	3.78	4.00
WF-1D008B5P	5	3.20	4.18	4.58	4.80
WF-1D008B6P	6	4.00	4.98	5.38	5.60
WF-1D008B7P	7	4.80	5.78	6.18	6.40
WF-1D008B8P	8	5.60	6.58	6.98	7.20
WF-1D008B9P	9	6.40	7.38	7.78	8.00
WF-1D008B10P	10	7.20	8.18	8.58	8.80
WF-1D008B11P	11	8.00	8.98	9.38	9.60
WF-1D008B12P	12	8.80	9.78	10.18	10.40
WF-1D008B13P	13	9.60	10.58	10.98	11.20
WF-1D008B14P	14	10.40	11.38	11.78	12.00
WF-1D008B15P	15	11.20	12.18	12.58	12.80
WF-1D008B16P	16	12.00	12.98	13.38	13.60
WF-1D008B17P	17	12.80	13.78	14.18	14.40
WF-1D008B18P	18	13.60	14.58	14.98	15.20
WF-1D008B19P	19	14.40	15.38	15.78	16.00
WF-1D008B20P	20	15.20	16.18	16.58	16.80

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. x. ±0.50 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: ±1°		TITLE: 0.8 Pitch C型 刺破公头胶壳						
		DWG. NO.: WF-1D008BXP			CHECKED: MAX			
		PART NO.: WF-1D008BXP			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	