








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 125V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$



合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

Part No	CKT	A	B	C	D
BTB0.544-10PLBDB2-MB42	2X5	2.00	3.20	4.70	4.10
BTB0.544-12PLBDB2-MB42	2X6	2.50	3.70	5.20	4.60
BTB0.544-14PLBDB2-MB42	2X7	3.00	4.20	5.70	5.10
BTB0.544-16PLBDB2-MB42	2X8	3.50	4.70	6.20	5.60
BTB0.544-18PLBDB2-MB42	2X9	4.00	5.20	6.70	6.10
BTB0.544-20PLBDB2-MB42	2X10	4.50	5.70	7.20	6.60
BTB0.544-22PLBDB2-MB42	2X11	5.00	6.20	7.70	7.10
BTB0.544-24PLBDB2-MB42	2X12	5.50	6.70	8.20	7.60
BTB0.544-26PLBDB2-MB42	2X13	6.00	7.20	8.70	8.10
BTB0.544-28PLBDB2-MB42	2X14	6.50	7.70	9.20	8.60
BTB0.544-30PLBDB2-MB42	2X15	7.00	8.20	9.70	9.10
BTB0.544-32PLBDB2-MB42	2X16	7.50	8.70	10.20	9.60
BTB0.544-34PLBDB2-MB42	2X17	8.00	9.20	10.70	10.10
BTB0.544-36PLBDB2-MB42	2X18	8.50	9.70	11.20	10.60
BTB0.544-38PLBDB2-MB42	2X19	9.00	10.20	11.70	11.10
BTB0.544-40PLBDB2-MB42	2X20	9.50	10.70	12.20	11.60
BTB0.544-44PLBDB2-MB42	2X22	10.50	11.70	13.20	12.60
BTB0.544-50PLBDB2-MB42	2X25	12.00	13.20	14.70	14.10
BTB0.544-60PLBDB2-MB42	2X30	14.50	15.70	17.20	16.60
BTB0.544-70PLBDB2-MB42	2X35	17.00	18.20	19.70	19.10
BTB0.544-80PLBDB2-MB42	2X40	19.50	20.70	22.20	21.60

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.20

X.XX:±0.10

ANGLES:

±1°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdTITLE:0.5 Pitch B型单槽立式BTB
母座业务图(单高4.4)无焊片镀金

PAR BTB0.544-XPLBDB2-MB42

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE1:1 UNIT:MM

SIZE:A4

SHEET:1F1

REV:A

CUSTOMER COPY