






技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$

序号	品名	材质
①	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式BTB母座吸盘	LCP UL94 V-0颜色:黑色.

High photosynthesis 合高 (H)	The female seat height 母座单高 (H1)	The male seat height 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.20

X.XX:±0.10

ANGLES:

±1°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdTITLE: 无柱
0.5 Pitch双槽立式BTB母(单高2.2)

PAR BTB0.522-XPLBSW1-MB42

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

SIZE:A4 SHEET:1F2 REV:A

CUSTOMER COPY

适用线路板

MANUFACTURE DWG		 东莞市讯普电子有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 无柱 0.5 Pitch双槽立式BTB母(单高2.2)	
			PAR	BTB0.522-XPLBSW1-MB43
DECIMALS:	ANGLES:		DWN	Lucas
X.:±0.50	±1°		CHKD	Ethan
X.X:±0.20			APVD	Jacob
X.XX:±0.10		SCALE:1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:2F2
			REV:A	