







High photosynthesis 合高 (H)	The female seat height 母座单高 (H1)	The male seat height 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$

序号	品名	材质
①	0.5 Pitch 双槽立式 BTB 母座胶芯	PA10T UL94 V-0 颜色: 黑色
②	0.5 Pitch 双槽立式 BTB 母座端子	铜合金 / 表面点镀金
③	0.5 Pitch 双槽立式 BTB 母座吸盘	LCP UL94 V-0 颜色: 黑色



MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE: 无柱
0.5 Pitch 双槽立式 BTB 母 (单高 3.0)

PAR BTB0.530-XPLBSW1-MB42

DECIMALS:

ANGLES:

X.: ± 0.50 $\pm 1^{\circ}$ X.X: ± 0.20 X.XX: ± 0.10

CUSTOMER COPY

SIZE: A4

SHEET: 1F2

REV: A

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

ROHS Compliant

MAPX

MODIFICATION

DATE

DRAW

APPROVE

A

B

C

D

E

F

G

H

I

J

PIN NO	PIN	DIM A	DIM B	DIM C	DIM E
BTB0.530-8PLBSW1-MB42	8	1.50	2.55	4.70	4.00
BTB0.530-10PLBSW1-MB42	10	2.00	3.05	5.20	
BTB0.530-12PLBSW1-MB42	12	2.50	3.55	5.70	
BTB0.530-14PLBSW1-MB42	14	3.00	4.05	6.20	
BTB0.530-16PLBSW1-MB42	16	3.50	4.55	6.70	
BTB0.530-18PLBSW1-MB42	18	4.00	5.05	7.20	
BTB0.530-20PLBSW1-MB42	20	4.50	5.55	7.70	
BTB0.530-22PLBSW1-MB42	22	5.00	6.05	8.20	
BTB0.530-24PLBSW1-MB42	24	5.50	6.55	8.70	
BTB0.530-26PLBSW1-MB42	26	6.00	7.05	9.20	
BTB0.530-28PLBSW1-MB42	28	6.50	7.55	9.70	
BTB0.530-30PLBSW1-MB42	30	7.00	8.05	10.20	
BTB0.530-32PLBSW1-MB42	32	7.50	8.55	10.70	
BTB0.530-34PLBSW1-MB42	34	8.00	9.05	11.20	8.00
BTB0.530-36PLBSW1-MB42	36	8.50	9.55	11.70	
BTB0.530-38PLBSW1-MB42	38	9.00	10.05	12.20	
BTB0.530-40PLBSW1-MB42	40	9.50	10.55	12.70	
BTB0.530-44PLBSW1-MB42	44	10.50	11.55	13.70	
BTB0.530-50PLBSW1-MB42	50	12.00	13.05	15.20	
BTB0.530-60PLBSW1-MB42	60	14.50	15.55	17.70	
BTB0.530-70PLBSW1-MB42	70	17.00	18.05	20.20	
BTB0.530-80PLBSW1-MB42	80	19.50	20.55	22.70	
BTB0.530-100PLBSW1-MB42	100	24.50	25.55	27.70	

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 无柱 0.5 Pitch 及 槽立式 BTB 等 (单高 3.0)
			PAR BTB0.530-XPLBSW1-MB42
DECIMALS:	ANGLES:		DWN Lucas
X.:±0.50	±1°		CHKD Ethan
X.X:±0.20			APVD Jacob
X.XX:±0.10		CUSTOMER COPY	
		SIZE:A4	SHEET:2F2
			REV:A

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15