






ROHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	0.5 Pitch D型 单槽侧插BTB母座胶芯	LCP UL94 V-0, 颜色: 本色		
②	0.5 Pitch D型 单槽侧插BTB母座端子	铜合金/表面镀金		

Part No	CKT	A	B	C	D
BTB0.553-4PWZDB4-MB42	2*2	0.50	2.54	3.50	2.20
BTB0.553-6PWZDB4-MB42	2*3	1.00	3.04	4.00	2.70
BTB0.553-8PWZDB4-MB42	2*4	1.50	3.54	4.50	3.20
BTB0.553-10PWZDB4-MB42	2*5	2.00	4.04	5.00	3.70
BTB0.553-12PWZDB4-MB42	2*6	2.50	4.54	5.50	4.20
BTB0.553-14PWZDB4-MB42	2*7	3.00	5.04	6.00	4.70
BTB0.553-16PWZDB4-MB42	2*8	3.50	5.54	6.50	5.20
BTB0.553-18PWZDB4-MB42	2*9	4.00	6.04	7.00	5.70
BTB0.553-20PWZDB4-MB42	2*10	4.50	6.54	7.50	6.20
BTB0.553-22PWZDB4-MB42	2*11	5.00	7.04	8.00	6.70
BTB0.553-24PWZDB4-MB42	2*12	5.50	7.54	8.50	7.20
BTB0.553-26PWZDB4-MB42	2*13	6.00	8.04	9.00	7.70
BTB0.553-28PWZDB4-MB42	2*14	6.50	8.54	9.50	8.20
BTB0.553-30PWZDB4-MB42	2*15	7.00	9.04	10.00	8.70
BTB0.553-32PWZDB4-MB42	2*16	7.50	9.54	10.50	9.20
BTB0.553-34PWZDB4-MB42	2*17	8.00	10.04	11.00	9.70
BTB0.553-36PWZDB4-MB42	2*18	8.50	10.54	11.50	10.20
BTB0.553-38PWZDB4-MB42	2*19	9.00	11.04	12.00	10.70
BTB0.553-40PWZDB4-MB42	2*20	9.50	11.54	12.50	11.20
.....	...	...	...	...	...
BTB0.553-80PWZDB4-MB42	2*40	19.50	21.54	22.50	21.20

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES				
DECIMALS:	ANGLES:	TITLE: 0.5 Pitch D型单槽侧插BTB母座业务图(单高5.3)		
X.: ±0.50	±1°	PAR	BTB0.553-XPWZDB4-MB42	
X.X: ±0.20		DWN	Lucas	
X.XX: ±0.10		CHKD	Ethan	
		APVD	Jacob	
		SCALE: 1:1	UNIT: MM	
		CUSTOMER COPY	SIZE: A4	SHEET: 1F1
				REV: A