





REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0		NEW RELEASE	07/12'21	JX	/	MOON




RECOMMENDED P.C.B LAYOUT
(TOLERANCE=±0.03mm)



备注:


1. 规格说明:

1. 塑胶 LCP 黑色
2. 端子 C2680 触点镀金0.8u”Min，
焊脚亮锡80u” Min， 镀镍30u” Min
3. 外壳 C2680 ,镀镍30u” Min
4. 额定电流 0.5A
5. 接触阻抗 30 MILLIONHM MAX
6. 绝缘阻抗 100 MEGOHMS MIN.
7. 额定电压 40V AC(RMS)
8. 工作温度 -25°C ~ 85°C
9. 耐久 10,000 CYCLES

MILLIMETERS	INCH	UNITS	 东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd									
X° ± 2'	X° ± 2'	MM	PART NUMBER:	TITLE: HDMT反沉3.37四脚四反弹片三个焊点								
.X ± 0.38	.XX ± 0.015	MAT'L										
.XX ± 0.25	.XXX ± 0.010	SEE NOTES										
.XXX ± 0.15	.XXXX ± 0.006	FINISH										
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		SEE NOTES	APPD:	DWG NO.: C-105410802--A-00								
		QTY	CHKD:	 <table><tr><td>SCALE</td><td>SHEET</td><td>REV.</td></tr><tr><td>1:1</td><td>1/2</td><td>A0</td></tr></table>			SCALE	SHEET	REV.	1:1	1/2	A0
		SCALE	SHEET				REV.					
		1:1	1/2	A0								
SEE NOTES	DR:											


RoHS

产品摆放方向



备注:

1. 卷装数量:600PCS/盘
2. 载带总长度




3. 每箱产品数量:3600PCS/CARTON



上带剥离角度:165°~180°
剥离力:20~130g

载带


产品摆放方向



DETAIL B



DETAIL B



MILLIMETERS	INCH	UNITS	MM	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			
X' ± 2'	X' ± 2'	MAT'L		PART NUMBER:		TITLE:	
.X ± 0.38	.XX ± 0.015	SEE NOTES		105410802-A		HDMI反沉3.37四脚四反弹片三个焊点	
.XX ± 0.25	.XXX ± 0.010	FINISH		APPD:		DWG NO.:	
.XXX ± 0.15	.XXXX ± 0.006	SEE NOTES		CHKD:		C-105410802-A-00	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			QTY	DR:		SCALE	SHEET
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			SEE NOTES			1:1	2/2
							REV.
							A0