



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:30mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PBT

Max.Processing Temp: 180°C for 30-60 seconds
(230°C for 10 seconds)

Dimension antitheses list

ITEM	A
Standard	3.00

Ordering Information

HC-CZ 254	- *	- N	- W	- *	- **	- *
No. of Rows	No. of Pins	Type	Length (Plastic)	Contact Plating	Contact Type	Contact Type
2= Dual Row	10/16/20Pin	2= 2Pin	(mm)	G0: Gold Flash	F= Female	M= Male
3= Three Row	32/44/48Pin	3= 3Pin		G1: 1u" Gold		
4= Four Row	64Pin	4= 4Pin		G2: 3u" Gold		
				G3: 5u" Gold		
				G4: 10u" Gold		
				G5: 15u" Gold		
				G6: 30u" Gold		
				S0: Gold Flash/Tin		
				S1: Tin		

	GENERAL TOLERANCE		制图			
			DRAWING			
		DIM	TOL	审核	产品名称	版 本
				CHECK	TITLE	REV.
		X.X	±0.30	批 准	HC-CZ254-3-N-W-12.89-XX-M	A
		X.XX	±0.20	APPROVAL	单位	mm
		X.XXX	±0.10	比 例	UNIT	
		Angle	±3.0°	SCALE	材料	1/1
1	初版发行	日期		投影		
序号	变更内容	日期		投影		
No.	MODIFY CONTENT	MODIFY DATE		Projection		