




CUSTOMER DRAWING




SCHEMATIC(SHORTING)

|        |                                                 |          |               |               |                 |              |               |                |               |        |
|--------|-------------------------------------------------|----------|---------------|---------------|-----------------|--------------|---------------|----------------|---------------|--------|
| H25    | 03                                              | XX       | X             | X             | X               | X            | X             | XX             |               |        |
| Series | Rating                                          | Function | Terminal Type | Actuator Type | Actuator Height | Housing Type | Terminal Type | Actuator Color | Housing Color | Suffix |
| 03     | 10A, 125VAC<br>6A, 250VAC<br>R(0.1A 125/250VAC) | 12       | S             | A             | 3mm             | N            | T1            | B              | B             |        |
|        |                                                 | 13       | P             | B             | 4mm             |              | T2            | W              | W             |        |
|        |                                                 | 14       |               | C             | 5mm             |              | T3            | R              | R             |        |
|        |                                                 | 22       |               |               |                 |              |               |                |               |        |
|        |                                                 | 23       |               |               |                 |              |               |                |               |        |
| 24     |                                                 |          |               |               |                 |              |               |                |               |        |
| ...    |                                                 | ...      |               |               | ...             |              |               |                |               |        |

MARKING

HAOTONG  
H25-0323SC/PC  
3(3)A 125/250VAC



PCB LAYOUT



佛山市皓通电子有限公司  
Foshan Haoswitch Electronic Co.,Ltd.

规格 Specification:

- 1.开关型号 Model No.:H25-0323PC
- 2.额定值 Rating:3(3)A 125/250VAC
- 3.接触电阻 Contact resistance:≤30 mΩ
- 4.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 5.电气寿命 Electronics life: > 10000 cycles
- 6.操作力 Operation force:500±150gf
- 7.所有材料符合 Rohs 要求 All materials are Rohs compliant

| DRAWN BY    | 制 图   | APLIN                           | 2026/01/08         | SCALE | 比例  | FREE         | PRODUCT NAME | 产品名称 | SLIDE SWITCH |
|-------------|-------|---------------------------------|--------------------|-------|-----|--------------|--------------|------|--------------|
| CHECKED BY  | 核 对   | APLIN                           | 2026/01/08         | PAGE  | 1/1 |              | DESCRIPTION  | 产品描述 |              |
| APPROVED BY | 批 准   | ZHANG                           | 2026/01/08         | UNIT  | mm  | PROJECTED 投影 | PART NO.     | 物料编号 |              |
| TOLERANCE   | 未标注公差 | X: ±0.5<br>X': ±0.3<br>XX: ±0.2 | X': ±5°<br>X': ±2° |       |     |              |              |      |              |