




CUSTOMER DRAWING



MARKING

HAOTONG
H25-0322PC
3(3)A 125/250VAC

CIRCUIT

H25 Series	03	XX	X	X	X	X	X	XX		
Rating	10A 125VAC 6A 250VAC 8(3)A 125/250VAC	Function	Terminal Type	Actuator Type	Actuator Height	Housing Type	Terminal Type	Actuator Color	Housing Color	Style
03	12		S	A	3mm		T1	B	B	
	13		P	B	4mm		T2	W	W	
	14		P	C	5mm	N	T3	R	R	
	...				...	R	T4			
	22						T5			
	23									
	24									
	...									

规格 Specification:

- 1.开关型号 Model No.:H25-0322PC
- 2.额定值 Rating:3(3)A 125/250VAC
- 3.接触电阻 Contact resistance:≤30 mΩ
- 4.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 5.电气寿命 Electronics life:＞10000 cycles
- 6.操作力 Operation force:400±150gf
- 7.所有材料符合Rohs要求 All materials are Rohs compliant
- 8.出厂使用需知：30天之后使用，需烘烤6个小时，温度110℃，再进行使用（尼龙9T特性），样品需要手焊。



佛山市皓通电子有限公司
Foshan Haoswitch Electronic Co.,Ltd.

DRAWN BY	APLIN	SCALE	FREB	PRODUCT NAME	SLIDE SWITCH
CHECKED BY	APLIN	PAGE	1/1	DESCRIPTION	
APPROVED BY	ZHANG	UNIT	mm	PART NO.	H25-0322PC-SNT1ZBB-T
TOLERANCE	X: ±0.5 X': ±0.3 XX: ±0.2	PROJECTED 投影		DRAWN NO.	HTDW20260108-601