


CUSTOMER DRAWING



PCB LAYOUT

H25	03	XX	X	X	X	X	X	X	XX
Series	Rating	Function	Terminal Type	Actuator Type	Actuator Height	Housing Type	Terminal Type	Actuator Color	Housing Color
10A 125VAC 6A 250VAC H25A 125/250VAC	12 13		S P		3.3mm 4mm 5mm		T1 T2 T3 T4 T5	B W R	B W R
03	14		PCB Terminal		...		T1 T2 T3 T4 T5	W R	Black White Red
...	22		...		...		T1 T2 T3 T4 T5	...	...
...	23		...		...		T1 T2 T3 T4 T5	...	...
...	24		...		...		T1 T2 T3 T4 T5	...	...

规格 Specification:

- 1.开关型号 Model No.:H25-0322PC
- 2.额定值 Rating:3(3)A 125/250VAC
- 3.接触电阻 Contact resistance:≤30 mΩ
- 4.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 5.电气寿命 Electronics life:≥10000 cycles
- 6.操作力 Operation force:400±150gf
- 7.所有材料符合Rohs要求 All materials are Rohs compliant
- 8.出厂使用需知: 30天之后使用, 需烘烤6个小时, 温度110℃, 再进行使用 (尼龙9T特性) , 样品需要手焊。



佛山市皓通电子有限公司
Foshan Haoswitch Electronic Co.,Ltd.

MARKING

HAOTONG
H25-0322PC
3(3)A 125/250VAC

SCHEMATIC(SHORTING)
开关短路型电路, 先通后断

DRAWN BY	制 图	APLIN	2026/01/08	SCALE	FREB	PRODUCT NAME	SLIDE SWITCH
CHECKED BY	核 对	APLIN	2026/01/08	PAGE	1/1	DESCRIPTION	
APPROVED BY	批 准	ZHANG	2026/01/08	UNIT	mm	PART NO.	
TOLERANCE	未标注公差	X: ±0.5 X': ±0.3 XX: ±0.2	Y: ±5° Y': ±2°	PROJECTED	投影	H25-0322PC-7NT1ZWV-TST	