




P.C.B LAYOUT



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 250±80gf.
- 6.Travel: 0.25±0.1mm.
- 7.life test: 100,000 cycles.
- 8.Operation temperature range: -25℃~85℃.
- 9.Sign"* "is importance dimension.

邮箱: hooya89@hooya.hk

电话: 0769-82310511-867

LED COLOR

Red	Yellow	Green	Blue	White	Pure Green	Red Yellow	Red Green	Red Blue	Yellow Green
-----	--------	-------	------	-------	------------	------------	-----------	----------	--------------

NO.	PART NAME	MATERIAL	QTY	FINISHING
5	TERMINAL	BRASS	4	Ag-PLATED
4	CONTACT	SUS	1	
3	BUTTON	PA66	1	
2	FIXITY	PPA	1	
1	HOUSING	PA66	1	

TOLERANCE UNLESS SPECIFIED								
<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
		NO	DATE	REVISIONS			BY	APPD
TITLE:TACT SWITCH				UNIT : MM	ROHS	DWN		
MODEL: TC-1193RE-L-E-C2-01				SCALE: 1:1	COMPLIANT	CHK'D		
 皓宇 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司						APPD		
						PRO.AGL:  		