


SCHEMATIC






P.C.B LAYOUT

邮箱: hooya89@hooya.hk
电话: 0769-82310511-867

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $25\pm 10gf$.
- 6.life test: 100000 cycles.
- 7.operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
- 8.Travel: $0.3^{+0.3}_{-0.2}mm$
- 9.Sign "*" is importance dimension.



					TOLERANCE UNLESS SPECIFIED							
					<1.5: $\pm 0.1mm$ >1.5~5.0: $\pm 0.25mm$ >5.0: $\pm 0.3mm$	ANGULAR $\pm 1^{\circ}$						
5	TERMINAL	PHOSPHOR BRONZE	4	Ag-PLATED			NO	DATE	REVISIONS		BY	APPD
4	HOUSING	LCP	1	BLACK	TITLE: TACT SWITCH		UNIT : MM		ROHS	DWN		
3	SPRING	SUS	1	Au-PLATED	MODEL: TC-0721U-08		SCALE: 1:1		COMPLIANT	CHK'D		
2	COVER	SUS	1							APPD		
1	KNOB	LCP	1	BEIGE								
NO.	PART	NAME	MATERIAL	QTY	FINISHING						PRO.AGL:	REV :A0



HOOYAELEC.COM
东莞市弘皓电子有限公司

PRO.AGL: REV :A0