

H
G
F
E
D
C
B
A

8 7 6 5 4 3 2 1

REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

- UL标准 (UL Standard)
- 1. 额定电压与电流: 300V/15A
Rated voltage/Rated current:300V/15A
 - 2. 功频耐压: AC1600V/Min
Withstanding Voltage:AC1600V/Min
 - 3. 线径范围: 28~12AWG
Wire range:28~12AWG
- IEC标准 (IEC Standard)
- 额定电压与电流: 320V/20A
Rated voltage/Rated current: 320V/20A

- NOTE 2:
- 1. 间距 (Pitch): 5.08mm
 - 2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
 - 3. 剥线长度: 7~8mm
Stripping length: 7~8mm
 - 4. 符合RoSH环保要求
RoHS Compliance
 - 5. 未标注公差表
Undimensioned tolerances

P距方向公差 (mm)		其他尺寸公差 (mm)							
Pitch range in mm		Nominal dimension range in mm						□	□
≤6	6~10	10~24	≤30	30~60	60~100	100~150	>150	0.1/10	□
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1'	□

- 订购方式 (HOW TO ORDER)
- MX2EDGKR-5.08-□□P-□ - □ - □□□□
- 型号
Series NO.




间距
Pitch

极数
Poles

客户型号
Customer Request
1. 单间距
Single Pitch

2. 双间距
Double Pitch
- 颜色 (Color)

1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)



4	(Cage)方盒	(Copper alloy)铜合金	(Ni plated)镀镍	PART NO.:	安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.			
3	(Contact)触点	(Copper alloy)铜合金	(Sn plated)镀锡	APPD:				
2	(Screw)螺丝 M3.0	(Steel)钢	(Zn plated)镀锌	CHKD:				
1	(Housing)塑件	PA66	UL94V-0	DRFT:				
ITEM	NAME OF PART	MATERIAL	NOTES	THIRD ANGLE PROJECTION	型号	MX2EDGKR-5.08-XXP-1X-XXAH		
					系列	MX2EDGKR-5.08	页码	1/1
					图号	MX2EDGKR508001	比例	1:1

8 7 6 5 4 3 2 1