

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.22	阿树

Specifications:

规格:





Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range: -40℃ - +105℃
温度范围: -40℃ - +105℃
Insulation resistance: ≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance: ≤20mΩ
接触电阻: ≤20mΩ
Material: PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category: 1U"Gold
镀层: 1U"Gold
Wave soldering temperature: 255±5℃, 10S
波峰焊温度: 255±5℃, 10S

PART NO.:

X1321 W R-2x11 J-C40 D18
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:2xXX-2x01~2x40P
⑤Plastic Height:J=1.0mm
⑥Pin Length:C=4.0mm
⑦Pin Length:D=1.8mm

X1321WR-2x11J-C40D18		PA6T	Brass	X1321F
PART NO		Material	Material(Pin)	Suitable XKB Female
DESIGN	阿树	VIEW: 	MODEL TYPE: 1.27mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X1321WR-2x11J-C40D18	
APPROVED		SIZE: A4	DWG NO.: X-X1321WR-2x11J-C40D18	
		SCALE	PAGE	REVISION
		N/A	1/1	A1



P.C.B LAYOUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED