

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.5	阿树

Specifications:
规格:
Voltage rating:400V AC/DC
额定电压: 400V AC/DC
Current rating:14A AC/DC
额定电流: 14A AC/DC
Withstanding voltage:1800V AC/minute
耐受电压: 1800V AC/分钟
Temperature range:-40℃--+125℃
温度范围: -40℃--+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max

PART NO.:

X3501 H-03 B-N0
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~12P
④Category:
A:TPA Type, A KEY Black
B:TPA Type, B KEY Nature
A0:Standard, A KEY Black
B0:Standard, B KEY Nature
⑤Material:N0-Nylon UL94V-0

Poles	Dimensions	
	A	B
02	3.50	8.00
03	7.00	11.50
04	10.50	15.00
05	14.00	18.50
06	17.50	22.00
07	21.00	25.50
08	24.50	29.00
12	38.50	43.00

X3501H-03B-N0	Nylon	H-XXA / H-XXA0 H-XXB / H-XXB0	X3501W-A X3501W-B	X3501T	X3501HL
PART NO	Material	Category	Suitable XKB Wafer	Suitable XKB Terminal	Category

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 3.5mm Crimp Style Connector		
PART NO.: X3501H-03B-N0		
DWG NO.: X-X3501H-03B-N0		
SCALE	PAGE	REVISION
N/A	1/1	A1