



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.14	阿树



Voltage rating:500V AC/DC
额定电压:500V AC/DC
Current rating:1.0A
额定电流: 1.0A
Insulation resistance:1000MΩ Min
绝缘电阻: 1000MΩ Min
Withstanding voltage:≥500V AC/minute
耐压: ≥500VC/分钟
Temperature range: -40℃ - +125℃
使用温度: -40℃ - +125℃



P.C.B Layout

PART NO.:

X1270 W V S-2x32 A2-6T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way:S-SMT
⑤Row No.-Pin No.:2xXX-2x03P~2x40P
⑥A2:1.27x2.54mm
⑦Material:6T-Nylon PA6T UL94V-0
⑧Planting Category:V01-All Gold Flash
SW-Matte tin

Poles	A	B	C
2x03	11.37	9.77	2.54
2x04	12.64	11.04	3.81
2x05	13.91	12.31	5.08
2x06	15.18	13.58	6.35
2x07	16.45	14.85	7.62
2x08	17.72	16.12	8.89
2x09	18.99	17.39	10.16
2x10	20.26	18.66	11.43
2x12	21.53	19.93	12.70
2x13	24.07	22.47	15.24
2x15	26.61	25.01	17.78
2x17	29.15	27.55	20.32
2x20	32.96	31.36	24.13
2x22	35.50	33.90	26.67
2x25	39.31	37.71	30.48
2x30	45.66	44.06	36.83
2x34	50.74	49.14	41.91
2x40	58.36	56.76	49.53



X1270WVS-2x32A2-6TSW	Nylon-6T UL 94V-0	Brass	Matte tin	X1270HA2-XXB
X1270WVS-2x32A2-6TV01			Gold Flash	X1270HA2-XXA
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing
MODEL TYPE: 1.27mm BTB Style Connectors				
PART NO.: X1270WVS-2x32A2-6TV01				
DWG NO.: X-X1270WVS-2x32A2-6TV01				
SCALE	PAGE	REVISION		
N/A	1/1	A1		

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 1.27mm BTB Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X1270WVS-2x32A2-6TV01
APPROVED		SIZE:	A4	DWG NO.: X-X1270WVS-2x32A2-6TV01