









SPECIFICATIONS

- Voltage rating:100V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:300V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥100MΩ
- Contact resistance:≤20mΩ


PART NO.:

X1004 W R S-08 A HF-4T SW
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Welding Way:S-SMT
⑤Row No.Pin No:XX-02~12Pin
⑥Special No:A-Outer Lock
⑦HF-Halogen Free
⑧Material:4T-PA4T UL94V-0
⑨Plating:SW-Matte Tin Plating 100u" Min.overall,
Ni 50u"Min.under Plating
V01-Gold Flash overall,Ni 50u Min under Plating

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面新增其他pin数样式说明, 升级整理图面	2024.9.28	阿树



SCALE 1:2

Poles	Dimensions(mm)				
	A	B	C	D	D
03	5.00	2.00	4.20	2.40	3.45
04	6.00	3.00	5.20	3.40	4.45
05	7.00	4.00	5.20	3.40	5.45
06	8.00	5.00	6.20	3.40	6.45
12	14.00	11.00	7.00	3.40	12.45

X1004WRS-08AHF-4TSW	PA4T	Phosphor Bronze	X1004H-B
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.00mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1004WRS-08AHF-4TSW
APPROVED		SIZE: A4	DWG NO.: X-X1004WRS-08AHF-4TSW