






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.23	阿树



Circuit diagram



P.C.B. LAYOUT



DMX-XXXP-X

1:1A以下
3:3A

1:转换型 SPDT		2:常闭型 SPST-NC		3:常开型 SPST-NO	
AuGLAR	±5°				
X.	±0.40				
X.x	±0.30				
X.xx	±0.20				
X.xxx	±0.15				
UNSPECIFIED TOLERANCES					

 117	 135
 150	 180
 12U	 16U
 115G	 151U
 141U	 000

DESIGN	阿树	VIEW:	MODEL TYPE: MICRO SWITCH
CHECKED		UNIT: mm/in	PART NO.: DM3-117P-1
APPROVED		SIZE: A4	DWG NO.: X-DM3-117P-1
XKB INDUSTRIAL PRECISION CO.,LIMITED		SCALE	PAGE
		N/A	1/1
		REVISION	A1