



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.03	阿树




- SPECIFICATIONS
- Voltage rating:150V AC/DC
 - Current rating:1A AC/DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥500MΩ
 - Contact resistance:≤30mΩ




PART NO.:

X1255 T-P V01
① ② ③ ④


- ①Series No
②Category:T-Terminal
③Material:P-Phosphor bronze
④Plating style:V01-Gold Flash;
SN-Bright tin plating



SECTION:C-C



SECTION:A-A



SECTION:B-B

X1255T-PV01	Phospho Bronze	AWG#28-32	0.90mm(Max)	Stamping Before Plating:30u" Ni;Whole Gold:Gold Flash	X1255H
X1255T-PSN				Stamping Before Plating:30u" Ni;70u" Sn Min	
PART No	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.25mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X1255T-PV01
APPROVED		SIZE:	A4	DWG NO.:	X-X1255T-PV01