



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.04.29	阿树




BOTTOM VIEW

X05ADGWA3DY4027


1:Au=1U"
3:Au=3U"
4:Au=6U"
5:Au=15U"
6:Au=30U"




FRONT VIEW



LEFT SIDE VIEW




BACK VIEW




MATERIAL 材料:
HOUSING 外壳: PBT,UL94V-0,BLACK.
TERMINAL 端子: PHOSPHOR BRONZE , ϕ =0.46MM,
GOLD PLATING ON CONTACT AREA.
SHIELD 保护物:C2680,T=0.20MM,20 MIN NICKEL PLATING
ON ALL AREA.

MECHANICAL 机械:
DURABILITY 耐用性: 750 CYCLES MIN.12.5MM/MINUTE
INSERTION FORCE 插入力: 2.2KG.F MAX
RETENTION STRENGTH 固位力: 7.7KG.F BETWEEN JACK AND PLUG
OPERATING TEMPERATURE 工作温度: -40°C~+85°C.
STORAGE TEMPERATURE 储存温度: -40°C~+85°C.
ALL CRITICAL DIMENSIONS WITH "★"

ELECTRICAL 电动:
VOLTAGE 电压:125 VOL TS AC
CURRENT RATING 额定电流:1.5AMP
DIELECTRIC STRENGTH 介电强度:1000 VAC RMS 50HZ OR 60HZ,1MIN
INSULATION RESISTANCE 绝缘电阻:500 MEGA OHMS MIN.INITIAL
AFTER 500V DC FOR 1 MINUTE
CONTACT RESISTANCE 接触电阻:SINGLE TERMINAL 30 MILLIOHMS MAX
INITIAL 50 MILLIOHMS MAX.AFTER
DURABILITY TEST



TOP VIEW



RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: RJ JACK
CHECKED		UNIT: mm/in	PART NO.: X05ADGWA3DY4027
APPROVED		SIZE: A4	DWG NO.: X-X05ADGWA3DY4027
SCALE N/A			PAGE 1/1
			REVISION A1