






PART NO.:

X2026 W V S-2x10 D1-LP SW
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Welding Way: S-SMT
- ⑤Row No.Pin No:2xXX-2x01P~2x22P
- ⑥Plug the Pin&Special NO:
D1-With Lock in the middle
- ⑦Matiral:LP-LCP;46-PA46
- ⑧Plating Category:SN-Bright Tin Plated
SW-Fog Tin Plated

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城
Connection

Specifications (规格):

1. Voltage rating(额定电压):250V AC DC
2. Current rating(额定电流):3.0A AC/DC
3. Withstanding voltage(耐压值): $\geq 800V$ AC/minute
4. Insulation resistance(绝缘电阻):1000M Ω Min
5. Contact resistance(绝缘电阻):10m Ω Max
6. Temperature range(使用温度):-40 $^{\circ}C$ ~+105 $^{\circ}C$

NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C	NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C
2X02	2.00	6.00	3.00	2X13	24.00	28.00	21.00
2X03	4.00	8.00	3.00	2X14	26.00	30.00	23.00
2X04	6.00	10.00	3.00	2X15	28.00	32.00	25.00
2X05	8.00	12.00	5.00	2X16	30.00	34.00	27.00
2X06	10.00	14.00	7.00	2X17	32.00	36.00	29.00
2X07	12.00	16.00	9.00	2X18	34.00	38.00	31.00
2X08	14.00	18.00	11.00	2X19	36.00	40.00	33.00
2X09	16.00	20.00	13.00	2X20	38.00	42.00	35.00
2X10	18.00	22.00	15.00	2X21	40.00	44.00	37.00
2X11	20.00	24.00	17.00	2X22	42.00	46.00	39.00
2X12	22.00	26.00	19.00				

X2026WVS-2x10D1-LPSW	LCP/PA46	BRASS	TIN-PLATED	X2026H-D
PART NO.	MATERIAL	MATERIAL(PIN)	FINISH(PIN)	Suitable XKB Terminal

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: x2026WVS-2x10D1-LPSW
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1