








Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x02	2.54	12.68	2x12	27.94	38.08
2x03	5.08	15.22	2x13	30.48	40.62
2x04	7.62	17.76	2x15	35.56	45.70
2x05	10.16	20.30	2x17	40.64	50.78
2x06	12.70	22.84	2x20	48.26	58.40
2x07	15.24	25.38	2x25	60.86	71.10
2x08	17.78	27.92	2x30	73.70	84.15
2x09	20.32	30.46	2x32	78.74	89.00
2x10	22.86	33.00			

DESIGN	阿树	VIEW: 	MODEL TYPE: 2.54mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X9555WR-2x06-6TV01		
APPROVED		SIZE: A4	DWG NO.: X-X9555WR-2x06-6TV01		
PRECISION CO., LIMITED			SCALE		
			N/A	1/1	A1



X9555 W R-2x06-6T V01
① ② ③ ④ ⑤ ⑥ ⑦

-



AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAuCES	

XK13 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED