










REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.17	阿 树



■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:5A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ

PART NO.:

X3025 W R-10-LP SW
① ② ③ ④ ⑤ ⑥

- ① Series No
② Category:W-Wafer
③ Welding Board Angle:R-Stright 90°
④ Row No-Pin No: XX-02P~12P
⑤ Material:LP-LCP UL94V-0
⑥ Planting:SW-Matte Tin
V01:Gold 1u"

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
02	3.00	9.65	08	21.00	27.65
03	6.00	12.65	09	24.00	30.65
04	9.00	15.65	10	27.00	33.65
05	12.00	18.65	11	30.00	36.65
06	15.00	21.65	12	33.00	39.65
07	18.00	24.65			

X3025WR-10-LPSW	LCP	Brass	Matte Tin	X3025HM-XX
X3025WR-10-LPV01			Gold 1u"	
PART NO	Material	Material(Pin)	Finish	Suitable XKB Housing

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

DESIGN	阿 树	VIEW:				MODEL TYPE: 3.00mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X3025WR-10-LPSW			
APPROVED		SIZE: A4	DWG NO.: X-X3025WR-10-LPSW			
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION	
			N/A	1 / 1	A1	