




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.23	阿树

Specifications:
规格:
1.Voltage rating:500VAC/DC
额定电压: 500V AC/DC
2.Current rating:3A AC/DC
额定电流: 3A AC/DC
3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
4.Temperature range: -55℃~+125℃
温度范围: -55℃~+125℃
5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
6.Contact resistance:30mΩMax
接触电阻: ≥30mΩ
Material:
材料:
7.Rubber core:PBT+30%GF UL94V-0
胶芯: PBT +30%GF UL94V-0
8.The iron shell:STEEL Nivkel Plating/
铁壳: STEEL,镀镍
9.Terminal:Brass
端子: 黄铜

PART NO.:
X12 25 F P 7 B 1
① ② ③ ④ ⑤ ⑥ ⑦
①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :F-Female
④P:Punch-pin
⑤Planting Categorty:7:AuSn
⑥Color:B-BLACK
⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3;

NUMBER OF POSITIONS	DIMENSION			
	A	B	C	D
9	16.35	24.99	30.80	19.10
15	24.75	33.30	39.20	27.60
25	38.35	47.04	53.05	41.10
37	54.75	63.50	69.40	57.30

铆合方式	TYPE-1:铆合	TYPE-2:前铆实心螺母	TYPE-3:后铆空心螺母
图示			

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCE	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X1225FP7B1
APPROVED		SIZE: A4	DWG NO.: X-X1225FP7B1

SCALE	PAGE	REVISION
N/A	1/1	A1