



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.05.22	



PART NO.:

X02 09 F I 1 B 5

Series N0.
Row No.Pin No.XX-09;15;25;37
Welding Board Angle :F-Female
T Tradutional C Car-pin
Planting Category: 1:1U' 2:2U' 3:3U' 4:5U'
5:15U' 6:30U' 7:AuSn
Color:B-BLACK W-White BL-Blue
1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7



Specifications:

- 1.Voltage rating:250VAC/DC
250V AC/DC
- 2.Current rating:3A(T) / 5A(C) AC/DC
: 3A(T) / 5A(C) AC/DC
- 3.Withstanding voltage:500V AC/minute
≥500V AC/
- 4.Temperature range: -55 -+105
-55 -+105
- 5.Insulation resistance:1000MΩMIN
≥1000MΩ
- 6.Contact resistance:30mΩMax
≥30mΩ

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	30.80	24.99	16.35	19.28
15	39.20	33.32	24.75	27.51
25	53.05	47.04	38.35	41.28
37	69.40	63.50	54.75	57.71

Material

- 7.Rubber core:PBT UL94V-0
PBT UL94V-0
- 8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating
SPCC, /
- 9.Terminal C2680
C2680
R



	TYPE-1:	TYPE-2:	TYPE-7:	TYPE-5:

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	
CHECKED	
APPROVED	

VIEW:	MODEL TYPE: D-SUB
UNIT: mm/in	PART NO.: X0209FT1B5
SIZE: A4	DWG NO.: