



Code-x	H(mm)	H1(mm)	ø(mm)		Code-x	H(mm)	H1(mm)	ø(mm)
A	4.30	3.15	3.50		O	11.00	9.85	3.00
B	4.50	3.35						
C	5.00	3.85						
D	5.50	4.35						
E	6.00	4.85						
F	6.50	5.35	3.40		T	13.50	12.35	
G	7.00	5.85						
H	7.50	6.35						
I	8.00	6.85	3.30		V	15.00	13.35	
J	8.50	7.35						
K	9.00	7.85						
L	9.50	8.35	3.10		W	15.50	14.35	
M	10.00	8.85						
N	10.50	9.35						
		3.00			X	16.00	14.85	
					Y	17.00	15.85	
					Z	18.00	16.35	
					19	19.00	17.85	



PCB.WELDING DRAWING

SPECIFICATION

Contact Rating:	50mA, 12V DC
Contact Resistance:	100mΩ max
Insulation Resistance:	100MΩ min. 500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-40℃~+85℃
Storage Temp:	-40℃~+85℃

PAPT NO	TC-1102HJ-C-G
Operating Force	A:100gf B:160gf C:260g
Height	Code-X

⑤	Terminal	2	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PA46	
②	Cover	1	Spcc	Plating Nickel
①	Keystake	1	PA46	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAUCES

XKLB 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: TACT SWITCH		
CHECKED		UNIT: mm/in	PART NO.: TC-1102HJ-C-G		
APPROVED		SIZE: A4	DWG NO.: TC-1102HJ-C-G		
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1	REVISION A1