







	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.02.29	桑葚
A1	N/A		图面升级整理图面	2025.12.26	阿树

Specifications (规格):

PART NO.:

X2026 W V S-2x14 D1-LP SW
 (1) (2) (3) (4) (5) (6) (7) (8) (9)

NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C	NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C
2X02	2.00	6.00	3.00	2X13	24.00	28.00	21.00
2X03	4.00	8.00	3.00	2X14	26.00	30.00	23.00
2X04	6.00	10.00	3.00	2X15	28.00	32.00	25.00
2X05	8.00	12.00	5.00	2X16	30.00	34.00	27.00
2X06	10.00	14.00	7.00	2X17	32.00	36.00	29.00
2X07	12.00	16.00	9.00	2X18	34.00	38.00	31.00
2X08	14.00	18.00	11.00	2X19	36.00	40.00	33.00
2X09	16.00	20.00	13.00	2X20	38.00	42.00	35.00
2X10	18.00	22.00	15.00	2X21	40.00	44.00	37.00
2X11	20.00	24.00	17.00	2X22	42.00	46.00	39.00
2X12	22.00	26.00	19.00				

X2026WVS-2x14D1-LPSW	LCP/PA46	BRASS	TIN-PLATED	X2026H-D
PART NO.	MATERIAL	MATERIAL(PIN)	FINISH(PIN)	Suitable XKB Terminal

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: x2026WVS-2x14D1-LPSW
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1