




Recommend PCB Layout



X2510 W V - 04 SP- N0SN

① ②③④⑤ ⑥ ⑦ ⑧ ⑨

- ①Series No.
②Category:
W-wafer
③Welding Board Angle:
V-180°
④Welding Way:
Blank-DIP
⑤Row No.-Pin No.
XX-Single row
⑥Special NO.
SP-Short of back
⑦Material:
N0-PA66 94V-0
⑧Planting Category:
V**:All Gold-Plated
*01-Gold Flash ; *02-2U" ; *03-3U" ; *05-5U"
*10-10U" ; *15-15U" ; *30-30U" ; *50-50U"
SN-Bright tin plating 120U"Min. ;
SW-Fog Tin plating
⑨Color:
Blank-natural color

Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating: 3A AC / DC
额定电流: 3A AC / DC
Withstanding voltage: 800V AC/minute
耐压电压: 800V AC/minute
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance: ≤10mΩ
接触电阻:≤10mΩ
After environment testing: ≤20mΩ
环境试验后: ≤20mΩ

Poles	Dimensions (mm)	
	A	B
2	2.54	5.08
3	5.08	7.62
4	7.62	10.16
5	10.16	12.70
6	12.70	15.24
7	15.24	17.78
8	17.78	20.32
9	20.32	22.86
10	22.86	25.40
11	25.40	27.94
12	27.94	30.48
13	30.48	33.02
14	33.02	35.56
15	35.56	38.10
16	38.10	40.64
17	40.64	43.18
18	43.18	45.72
19	45.72	48.26
20	48.26	50.80

X2510WV-04SP-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54 mm Crimp Style Connectors		
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2510WV-04SP-N0SN		
Δx					4<L≤ 16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2510WV-04SP-N0SN		
Δx					16<L≤ 63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION				DATE	REVISED						APPROVED	L> 63	±0.5
REVISIONS							UNSPECIFIED TOLERANCES							
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0