



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.18	阿树






- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:10A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ

PART NO.:

X5050 W R-04-N0 SN XX
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:XX-04Pin
⑤Material:N0-PA66 UL94V-0
N2-PA66 UL94V-2
⑥Planting:SN-Bright Tin Plated
⑦Color: Blank-Natural Color



PCB LAYOUT

X5050WR-04-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X5050H
X5050WR-04-N2SNBK	Nylon 66 UL 94V-2 Black			
X5050WR-04-N2SN	Nylon 66 UL 94V-2			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	5.08mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X5050WR-04-N0SN
APPROVED		SIZE:	A4	DWG NO.:	