






- X9556 W R -02-N0V01
- 11 12 13 14 15 16 17 18 19
- 11 Series No.
12 Category :
W-wafer
13 Welding Board Angle:
R-90°
14 Welding Way:
Blank-DIP
15 Row No.-Pin No.
XX-Single row
16 Special NO.
17 Material :
N0-PA66 94V-0
18 Planting Category:
V**All Gold-Plated
"01-1u" ; "02-2u" ; "03-3u" ; "05-5u"
"10-10u" ; "15-15 u" ; "30-30u" ; "50-50u"
SN-Bright tin plating 70U"
SN1-Bright tin plating 120U"Min. ;
SW-Fog Tin plating
19 Color:
Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	2.54	7.62
3	5.08	10.16
4	7.62	12.70
5	10.16	15.24
6	12.70	17.78
7	15.24	20.32
8	17.78	22.86
9	20.32	25.40
10	22.86	27.94
11	25.40	30.48
12	27.94	33.02
13	30.48	35.56
14	33.02	38.10
15	35.56	40.64
16	38.10	43.18
17	40.64	45.72
18	43.18	48.26
19	45.72	50.80
20	48.26	53.34
21	50.80	55.88
22	53.34	58.42
23	55.88	60.96
24	58.42	63.50

X9556WR-02-N0V01	Nylon 66 UL 94V-0	Brass	Gold-Flash	X9556H
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

XKB						DSND		DATE		SCALE: N/A	MODEL TYPE:
ANGLAR						DWN		DATE		VIEW:	2.54 mm Crimp Style Connectors
L≤4						CHKD		DATE		UNIT: mm/in	PART NO.:
4<L≤16						APPD		DATE		SIZE: A4	X9556WR-02-N0V01
16<L≤63						DWG NO.:					X-X9556WR-02-N0V01
L>63						WEIGHT					1.0g
UNSPECIFIED TOLERANCES						SHEET					1/1
XKB INDUSTRIAL PRECISION CO.,LIMITED						REVISION					A0
REVISIONS											
www.helloxkb.com											
DESCRIPTION											
DATE											
REVISED											
APPROVED											
MARK											