








Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X2581 W R-08 - N0 SN

① ② ③ ④ ⑤ ⑥

- ① Series No.
 ② Category : W-WAFER
 ③ Wedding Board Angle : R-Stright 90°
 ④ Row No.-Pin No.: XX-02P~16P
 ⑤ Material : N0-PA66;46-PA46 94V-0
 ⑥ Plating Category: Sn-Bright Tin Plating



Recommend PCB Layout

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.50	7.50	12	27.50	32.50
03	5.00	10.00	13	30.00	35.00
04	7.50	12.50	14	32.50	37.50
05	10.00	15.00	15	35.00	40.00
06	12.50	17.50	16	37.50	42.50
07	15.00	20.00			
08	17.50	22.50			
09	20.00	25.00			
10	22.50	27.50			
11	25.00	30.00			

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connectors		
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2581WR-08-N0SN		
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2581WR-08-N0SN		
Δx					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4	XKB INDUSTRIAL PRECISION CO.,LIMITED		
Δx					16<L ≤ 63	±0.4								
MARK	DESCRIPTION				DATE	REVISED	APPROVED							
REVISIONS							UNSPECIFIED TOLERANCES							
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														