



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		新增螺母规格, 图面升级整理图面	2025.07.26	阿树





Specifications:
规格:
1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
2.Current rating:3A(T) / 5A(C) AC/DC
额定电流: 3A(T) / 5A(C) AC/DC
3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
4.Temperature range: -55℃~+105℃
温度范围: -55℃~+105℃
5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
6.Contact resistance:30mΩMax
接触电阻: ≥30mΩ
Material:
材料:
7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC,镀镍/镀锡/镀金
B、成品不能有弯针, R角不一致等不良。

PART NO.:

X02 09 W I Z BL Z
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
- ②Row No.Pin No.XX-09;15;25;37
- ③Welding Board Angle :W-Male
- ④T: Tradutlional C: Car-pin
- ⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn
- ⑥Color:B-BLACK W-White BL-Blue
- ⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7 6:TYPE-6

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	30.80	24.99	18.00	19.28
15	39.20	33.32	26.50	27.51
25	53.05	47.04	40.00	41.28
37	69.40	63.50	56.60	57.71



图示	TYPE-1: 铆合	TYPE-2: 前铆实心螺母	TYPE-7: 后铆鱼叉	TYPE-5: 铆鱼叉锁螺丝	TYPE-6: 铆鱼叉锁螺丝

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	D-SUB
CHECKED		UNIT:	mm/in	PART NO.:	X0209WT7BL7
APPROVED		SIZE:	A4	DWG NO.:	