




SCHEMATIC



邮箱: hooya89@hooya.hk
电话: 0769-82310511-867

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: A:100 $\pm$ 30gf/C:160 $\pm$ 50gf/E:250 $\pm$ 80gf.
- 6.Travel:0.25 $\pm$ 0.1mm.
- 7.life test: 1000000 cycles.
- 8.Operation temperature range:-25 $^{\circ}$ C~85 $^{\circ}$ C.
- 9.Sign"* "is importance dimension.

高度
✓ H=4.3mm
H=5.0mm
H=5.5mm
H=6.0mm
H=7.0mm
H=7.5mm
H=8.0mm
H=9.0mm
H=(10 - 27)mm

					TOLERANCE UNLESS SPECIFIED							
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2026.03.21	首次发行		LP	
5	KNOB	PA9T	1	BLACK/RED			NO	DATE	REVISIONS		BY	APPD
4	COVER	BRASS	1	Sn-Plating	TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN	
3	CONTACT	SUS	1	Ag-Plated	MODEL: TC-06104-043E-01-L100			SCALE: 1:1		COMPLIANT	CHK'D	
2	CASE	PA9T	1	BLACK	 DONGGUANG HAORYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司					APPD		
1	TERMINAL	BRASS	1	Ag-Plated								
NO.	PART	NAME		MATERIAL	QTY	FINISHING				PRO.AGL: 		REV :A0