

1.View and size(视图及尺寸)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55 ~ +150 ℃
3.IP Rating (防护级别)	IP 50
4.Diameter of socket end(插合端直径)	φ0.7
5.Testing Voltage (测试电压)	850V
6.Working Voltage (工作电压)	700V
7.Rated Current (额定电流)	7A
8.Shell material (壳体材质)	Brass (chromium plating)/(nickel plating) fixation ring/ 黄铜 (镀铬) / (镀镍) 固定圈
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10.Insulator material(绝缘体材质)	PPS


Sum up(总结)

Series(系列)	B
Shell style/model (外壳样式/型号)	ZGG-With a nut (post-fixed) 带有一个螺母(后固定)
Button (按键)	A button(一个按键)
Termination type (终止类型)	Female print PCB(印刷PCB)
Line diameter awg(线材直径)	30AWG-22AWG
Cable diameterφ(电缆直径)	0-0
Match plug(匹配插头)	TGG.0B.P04.CLA052H


Location pin combination(定位销组合)

(编号) Numder	Number of positioning pins(定位销数量)	Angle(角度)	Series(系列)-0B
G	One(1)		(Zero degrees)0°
A	Two(2)	A	Thirty degrees(30°)
B	Two(2)		Sixty degrees(60°)
C	Two(2)		Ninety degrees(90°)
D	Two(2)	β	135 degrees(135°)
E	Two(2)		145 degrees(145°)
F	Two(2)		155 degrees(155°)
J	Two(2)	Y	Forty-five degrees(45°)
K	Two(2)		Seventy degrees(70°)
L	Two(2)		80 degrees(80°)


	A	B	C√	ANGLE	
5-10	±0.02	±0.05	±0.1	0°-30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°-90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100-	±0.15%	±0.20%	±0.25%		



	A	N	L	E	S1	S2
MM	ø10	16.3	19.6	M9*0.6	8.2	11
in	0.39	0.64	0.77		0.32	0.43




Pcb plate opening size
(PCB板开孔尺寸)



Pane hole size
(面板开孔尺寸)



Boarded mother adhesive core
(板接型母胶芯)



Positive view of the socket
(插座正视图)

ZG G.0B.P04.C L N

Model(型号)

Positioning pin(定位销)

Series(系列)

Needle core configuration(针芯配置)

Outer casing(外壳)

Insulator(绝缘体)

Needle core(针芯)

DESIGNED (设计)	DATE (日期)	SCALE (比例)	N/A (不适用)	MODEL TYPE 型号类型: ZGG-08.P04.CLN
CHECKED (校对)	DATE (日期)	VIEW (视图)		PART NO. 0B4-core socket
APPROVED (审核)	DATE (日期)	UNIT (单位)	MM	名称: 0B4插座
REVISIONS		MATERIAL (材料)		DWG NO.:
www.helloxb.com www.helloxb.cn		XKB INDUSTRIAL PRECISION CO., LIMITED		HEIGHT (高度) SHEET 1/1 REVISION (修订) 0