








S:Scrolls



RECOMMEND PCB LAYOUT (THICKNESS=1.6mm)
TOLERANCE: ±0.05



F: Flat

Notes:

Specifications:

1. Current rating: 1 A Max.
2. Dielectric withstanding voltage: 100V(AC) for 1 min.
3. Contact resistance: 50m Ω Max.
4. Insulation resistance: 100M Ω Min.
5. Total mating force: 3.57 Kgf Max.
6. Total unmating force: 1.0 Kgf Min. 0.81~2.05 Kgf Min. after 10000 insertion/extraction cycles
7. Temperature range: -30°C~+80°C

Housing Material: LCP UL94V-0, black
Contact Terminal: PHOSPHOR BRONZE
Metallic Shell: SUS

U255-051N-4BH74-FS

1:AU 1U"
5:AU 15U"
6:AU 30U"

S:SUS
S:Scrolls
F:Flat

Δx					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS						
UNSPECIFIED TOLERANCES						
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	MICRO USB
CHKD		UNIT: mm/in	PART NO.: U255-051N-4BH74-FS
APPD		SIZE: A4	DWG NO.: U255-051N-4BH74-FS
			WEIGHT
			SHEET
			REVISION
			1/1
			A0