





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.14	阿树



Specifications:
规格:
Voltage rating:50V AC/DC
额定电压: 50V AC/DC
Current rating:0.5A AC/DC
额定电流: 0.5A AC/DC
Withstonding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range:-40℃--+105℃
温度范围: -40℃--+105℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max



PART NO.:
X0814 F V S-2x15 A -9T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:F-Female
- ③Welding Board Angle:V-Stright 180°
- ④Welding Way: S-SMT
- ⑤Row No.Pin No:2xXX-2x02~2x25P
- ⑥Height:A=2.9mm; B=3.4mm; C=3.9; C1=3.9
- ⑦Material:9T-PA9T UL94V-0
- ⑧Plating:V01-Gold Flash ;
SN-Tin Plated

Mating Height	PLUG	SOCKET	L	L1	C(Ref)
A=4.0	2.80	A=2.90	2.90	1.65	1.94
B=4.5	3.30				
C=5.0	3.80				
D=5.5	4.30	B=3.40	3.40	1.65	1.94
E=6.0	4.80				
F=6.5	5.30				
G=7.0	5.30	C=3.90	3.90	1.65	2.44
		C1=3.9	3.90	1.25	2.44

X0814FVS-2x15A-9TV01	Nylon 9T	Phosphor Bronze	X0814W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuces	



DESIGN	阿树	VIEW:		MODEL TYPE: 0.8mm BTB Connectors
CHECKED		UNIT:	mm/in	PART NO.: X0814FVS-2x15A-9TV01
APPROVED		SIZE:	A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1