




REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1:

UL标准 (UL Standard)

1. 额定电压与电流: 300V/15A
Rated voltage/Rated current: 300V/15A

IBC标准 (IBC Standard)

1. 额定电压与电流: 320V/10A
Rated voltage/Rated current: 320V/10A

NOTE 2:

1. 间距(Pitch): 5.00mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 引线长度: 7~8mm
Stripping length: 7~8mm
4. 符合RoHS环保要求
RoHS Compliance
5. 额定扭矩: 0.4N.m 3.54[Lb. in]
(Rated torque): 0.4N.m 3.54[Lb. in]
6. 未标注公差表
Undimensioned tolerances

断面方向公差 (mm)				其他尺寸公差 (mm)						
Pitch range in mm				Nominal dimension range in mm						
≤6	6 ~ 10	10 ~ 24		≤30	30 ~ 60	60 ~ 100	100 ~ 150	≥150	0.1/ ∠	
±0.15	±0.20	±0.30		±0.20	±0.30	±0.50	±0.70	±1.00	±1	

订购方式(HOW TO ORDER)

MX2EDGKA -5,00- P- - -

型号	间距	极数
Series NO.	Pitch	Poles

客户型号
Customer Request

1. 单间距
Single Pitch

2. 双间距
Double Pitch

顏色(Color)
1. 灰色(Gray) 2. 藍色(Blue)
3. 黑色(Black) 4. 綠色(Green)
5. 橙色(Orange) 6. 紅色(Red)
7. 黃色(Yellow) 8. 白色(White)
9. 透明(Transparent)


4	(Cage)方盒	(Copper alloy) 铜合金	(Ni plated)镀镍
3	(Contact)触点	(Copper alloy) 铜合金	(Ni plated)镀镍
2	(Screw)螺丝 M3	(Steel)钢	(Zn plated)镀锌
1	(Housing)罩件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.:

APPD:

CHKD:

DRFT:



THIRD ANGLE PROJECTION



安徽亿思特电子科技有限公司
ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.

型号

MX2EDGKA-5.00-XXP-1X-XXAH

系列	
----	--

MX2EDGKA-5.00

页码

1/1

图号	
----	--

MX2EDGKA500001

	比例
--	----

1:1
