




PCB LAYOUT

Specifications:
Voltage rating:250V AC/DC
Current rating:3A AC/DC
Withstanding voltage:400V AC/minute
Temperature range:-40℃~+125℃
Insulation resistance:≥800MΩ
Contact resistance:≤20mΩ
Housing:PA6T UL94V-0 Color:Black
Contact :Brass H65



X6511 W V -01 H - C60 D30
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-01~40P
- 5.Special:A-Half-AuSn
- 6.Plastic Height:H=2.5mm
- 7.Pin Length:C=6.0mm
- 8.Pin Pitch:D=3.0mm
- 9.Plating:Blank-Gold 1u"; V03-Gold 3u"
V15-Gold 15u"; V30-Gold 30u"

X6511WV-01H-C60D30	PA6T	Brass H65	X6511WV
PART NO	Material	Material(Pin)	Suitable XKB Female

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L≤ 4 ±0.2
Δx					4<L≤ 16 ±0.3
Δx					16<L≤ 63 ±0.4
Δx					L> 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm BTB Connector
DWN		VIEW:	PART NO.: X6511WV-01H-C60D30
CHKD		UNIT: mm/in	DWG NO.: X-X6511WV-01H-C60D30
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0