






REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A		图面升级整理图面	2025.06.07
A2	ECN-P-2026041301	A2X2	产品行程及按键材质变更	2026.04.13



额定范围 Rated range	50mA DDC12V
耐电压 Rate voltage current	AC250V 50Hz/1min
绝缘电阻 Insulted resistance	≥100MΩ
接触电阻 Contact resistance	≤50mΩ
环境温度 ambient temperature	-25℃~+70℃
相对湿度 relative humidity	(40℃) ≤60%
寿命 life	50,000 cycles Min
行程 Travel	0.1±0.05mm



CIRCUIT DIAGRAM



PAPT NO	TS-3025-A-B-A
Operating Force(±50gf)	A:160gf B:260gf C:350gf
Height	H:A:1.5 B:1.6 C:1.7
Fixed column	A:With B:without

E	Film	1	polyimide	Yellow
D	Contact	2	F.ag/SUS	Ag Plated-silvery white
C	Cover	1	SUS	silvery white
B	Base	1	LCP	Ag Plated-Black
A	Button	1	LCP	Black
ITEM	PAPT NAMF	QTY	MATERIAL	PLATED/COLOR

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	山楂	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TS-3025-A-B-A
APPROVED		SIZE:	A4	DWG NO.:	
				SCALE	PAGE
				N/A	1/1
				REVISION	A2

XKB INDUSTRIAL PRECISION CO.,LIMITED