

1

2

3

4


A

B


C

D



| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.06.23 | 阿树     |




Circuit diagram



P.C.B LAYOUT




MOUNTING SURFACE




DMX-XXXD-X

1:1A以下  
3:3A


| 1:转换型 SPDT             |       | 2:常闭型 SPST-NC                        |  | 3:常开型 SPST-NO |  |
|------------------------|-------|--------------------------------------|--|---------------|--|
|                        |       |                                      |  |               |  |
| AuGLAR                 | ±5°   |                                      |  |               |  |
| X.                     | ±0.40 |                                      |  |               |  |
| X.x                    | ±0.30 |                                      |  |               |  |
| X.xx                   | ±0.20 |                                      |  |               |  |
| X.xxx                  | ±0.15 |                                      |  |               |  |
| UNSPECIFIED TOLERAuces |       | XKB INDUSTRIAL PRECISION CO.,LIMITED |  |               |  |




117




135




150




180




12U




16U




115G



151U



141U



000

|          |    |          |       |             |               |
|----------|----|----------|-------|-------------|---------------|
| DESIGN   | 阿树 | VIEW:    |       | MODEL TYPE: | MICRO SWITCH  |
| CHECKED  |    | UNIT:    | mm/in | PART NO.:   | DM1-151UD-1   |
| APPROVED |    | SIZE:    | A4    | DWG NO.:    | X-DM1-151UD-1 |
|          |    | SCALE    | N/A   | PAGE        | 1/1           |
|          |    | REVISION | A1    |             |               |

1

2

3

4

A

B

C

D