







Circuit



LED RATING						
NO.	1	2	3	4	5	6
COLOR	Red	Yellow	Green	Blue	White	FULL Green
Ovltage	2.0~2.4V	2.4~2.7V	2.3~2.5V	3.3~3.6V	3.0~3.6V	3.0~3.6V
Current	20mA max					

双色灯：橙色，绿色



P. C. B Layout

8	COVER	PC	1		TOLERANCE UNLESS SPECIFIED							
7	FRAME	PA66	1									
6	LED	GaAsP/GAP	1		UP TO 5mm: ±0.1	ANGULAR	1					
5	HOUSING	PA66	1		ABOVE 5mm: ±0.2	±1°						
4	BUTTON	PA66	1		TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	1		MODEL: TC-1193RB-OG-C-C5A-02			SCALE: 1:1	COMPLIANT	CHK'D		
2	TERMINAL	BRASS	4	AG-PLATED	DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD				
1	STAND	SUS	1					PRO.AGL:				
NO.	PART NAME	MATERIAL	QTY	FINISHING								REV :A0