

NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/15A
Rated voltage/Rated current: 300V/15A
2. 功率耐压: AC1600V/Min
Withstanding Voltage: AC1600V/Min
IEC标准 (IEC Standard)
1. 额定电压与电流: 230V/20A
Rated voltage/Rated current: 230V/20A

NOTE 2:
1. 间距(Pitch): 5.00mm
2. 使用温度范围: -40℃~-105℃
Operating temperature: -40℃~-105℃
3. 符合RoHS环保要求
RoHS Compliance
5. 未标注公差表
Unindicated tolerances

刃面方向公差 (mm)			其他尺寸公差 (mm)						
Pitch range in mm			Nominal dimension range in mm						
≤6	6 10	10 24	≤30	30 60	60 100	100 150	>150	0.1/ ∠	
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1%	

订购方式(HOW TO ORDER)

MX2EDGR-5.00- -P- - - - -

型号 Series No.	间距 Pitch	极数 Poles	客户型号 Customer Request
------------------	-------------	-------------	--------------------------

顏色(Color)

1. 灰色(Gray) 2. 藍色(Blue)
3. 黑色(Black) 4. 綠色(Green)
5. 棕色(Orange) 6. 紅色(Red)
7. 黃色(Yellow) 8. 白色(White)
9. 透明(Transparent)

1. 单间距
Single Pitch

2. 双间距
Double Pitch

1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

N=No.of contacts

2	(Pin header) 焊脚	(Copper alloy) 铜合金	(Sn plated) 镀锡
1	(Housing) 罩件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.: /		 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.			
APPD: /		型号 MX2EDGR-5.00-XXP-1X			
CHKD: /					
DRFT: /					
 THIRD ANGLE PROJECTION		系列 MX2EDGR-5.00	页码 1/1		
		图号 MX2EDGR500001	比例 1:1		