



1

2

3

4



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.11.27	阿树
/	/		/	/	/

Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:2A AC/DC

额定电流: 1.0A AC/DC

Contact Resistance:≤20MΩ

接触电阻: ≤20MΩ

Insulation Resistance:≥100MΩ

绝缘电阻: ≥100MΩ

Dielectric strength:500V AC/minutenai

耐压: 500V AC/minute

PART NO.:

X9821 W V S-02-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

①Series No

②Category:W-Wafer


③Welding Board Angle:V-Stright 180°

④Welding Way: S-SMT

⑤Row No.Pin No:XX-02~16Pin

⑥Material:LP-LCP UL94V-0

⑦Planting: SN-Bright tin plating



D	Back cover	1	LCP	UL 94V-0,Color:Beige
C	Plain	2	Brass	SN-plated
B	Reeds	6	Phosphor Bronze	SN-plated
A	Pedestal	1	LCP	UL 94V-0,Color:Beige
NO	NAME	QTY	MATERIAL	FINISH

X9821WVS-02-LPSN	LCP UL 94V-0	Brass	Tin-Plated	X9821H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

PCB LAYOUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.25mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X9821WVS-02-LPSN
APPROVED		SIZE:	A4	DWG NO.:	X-X9821WVS-02-LPSN
		SCALE	N/A	PAGE	1/1
				REVISION	A1

1

2

3

4